


This chart shows the intensity of hotspots in the combinations of Alloy tape light and channels (with a frosted diffuser).

Hotspot values are the same for dry and wet location tapes; the measurements below were taken with dry location tape.

For example, the PrimaLine XT 1.5 Tape installed in a Duro 1 Channel exhibits no hotspots; the same tape installed in the Duro 2 channel exhibits hotspots with a level of 1 (seen in the image to the right).

Note: This chart shows perceived, not absolute, hotspot levels that are measured by the human eye and not a machine. Perceived values may differ slightly from individual to individual.



	Duro 1	Duro 2	Surfa 1	Surfa 2	Surfa 2X	Surfa 3	Surfa 6	Suspan 1	Ankr 1	Ankr 2	Ankr 3	Ankr 4	Naro 3	Naro 4	Hangr 1
PrimaLine® 1.5	0	1	5	2	0	5	5	0	1	0	0.5	0.5	1	5	0
PrimaLine 1.5 XT	0	1	5	n/a	0	n/a	5	0	1	0	0.5	0.5	n/a	5	0
PrimaLine 3	0	1	3	1	0	4.5	5	0	0	0	0	0	0.5	5	0
PrimaLine 3 XT	0	1	3	n/a	0	n/a	4	0	0	0	0	0	n/a	4	0
PrimaLine 4.4	0	1	4	3	0	5	5	0	1	0	1	1	3	5	0
PrimaLine 4.4 Gen 2 / 4.4 XT Gen 2	0	1	4	1	0	5	3	0	0	0	0	0	0	3	0
PrimaLine 5.5 LP	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
PrimaLine 6.6 Gen 2	n/a	n/a	n/a	n/a	0	n/a	1	0	0	0	n/a	n/a	n/a	1	0
PrimaLine 8 Gen 2	n/a	n/a	n/a	n/a	0	n/a	n/a	0	1	0	n/a	n/a	n/a	n/a	0
PrimaLine 3 SE	n/a	n/a	n/a	n/a	n/a	n/a	n/a	n/a	n/a	n/a	n/a	n/a	n/a	n/a	n/a
Varien™ 5.5 Dim-to-Warm	0	0	3-5**	2-4**	0	n/a	1-4**	0	4	0	5	5	n/a	1-4**	0
Radialux® 2.2 RGB*	0.5	3	4	5	2	5	5	0	1	0	1	1	2	5	0
Radialux 4.4 RGB*	0	1	4	2	0	5	5	0	2	2	1	1	1	5	0
Radialux 4.4 RGB-W*	n/a	n/a	n/a	n/a	n/a	n/a	5	0	1	0	n/a	n/a	n/a	5	0
Radialux 5.9 RGB-W*	n/a	n/a	n/a	n/a	0	n/a	5	0	3	0	n/a	n/a	n/a	5	0
Radialux 8.8 RGB*	n/a	n/a	n/a	n/a	1	n/a	n/a	0	4	0	n/a	n/a	n/a	n/a	0

n/a = tape light cannot be installed in this channel

* Tested at max. brightness with light blue color. Hotspot values will vary with color and brightness values.

** Hotspot levels vary depending on brightness: the first number is measured at full brightness, the second number at 10% brightness.